Desktop/Cartesian Type

Robot



SHOT mini™/SHOTMASTER™



MUSASHI's general-purpose desktop robot, the global de facto standard.



SHOTmini™/SHOTMASTER™ SX series Line up











SHOTmini 100SX

SHOTmini 200SX

SHOTMASTER 300SX

SHOTMASTER 400SX

SHOTMASTER 500SX

■ Specifications

Item name		SHOTmini100SX		SHOTmini 200SX		SHOTMAS	STER 300SX	SHOTMAS	STER 400SX	SHOTMAS	STER 500SX
Model		SM100SX- 3A-SS	SM200SX- 3A-SS	SM200SX- 3A-Z-SS	SM200SX- 4A-SS	SM300SX- 3A-SS	SM300SX- 4A-SS	SM400SX- 3A-SS	SM400SX- 4A-SS	SM500SX- 3A-SS	SM500SX- 4A-SS
No. of controlled axes			3-axis		4-axis	3-axis	4-axis	3-axis	4-axis	3-axis	4-axis
	X-axis, Y-axis	100mm	100mm 200mm			300mm 400mm 500mm					
ravel ranges	Z-axis		50mm					80	mm		
	W-axis		-		±360°	-	±360°	-	±360°	-	±360°
	X-axis, Y-axis				1 to 80	0 mm/s					
Setting range of PTP	Z-axis	1 to 350	1 to 350 mm/s 1 to 250					1 to 400 mm/s			
operation speed (*1)	W-axis		-		1 to 900°/s		1 to 900°/s		1 to 900°/s		1 to 900°/s
Setting range	X-axis, Y-axis			0.1 to 800 mm/s							
	Z-axis	0.1 to 35	0 mm/s	0.1 to 250 mm/s				0.1 to 400 mm/s			
operation speed (*1)	W-axis				0.1 to 900°/		0.1 to 900°/s		0.1 to 900°/s		0.1 to 900°/s
	X-axis, Y-axis					±0.0	01mm				
Repetitive positioning	Z-axis					±0.01mm					
accuracy (*2)	W-axis		1-1		±0.01°	-	±0.01°	-	±0.01°	-	±0.01°
1 (0)	Y-axis		8	kg				15	ōkg		
oading capacity (*3)	Z-axis	2k	g	3.5kg	2.5kg	7kg	6kg	7kg	6kg	7kg	6kg
Rated voltage and frequency						AC100-24	0V 50/60Hz				
Power consumption			100W		120W	200W	220W	200W	220W	200W	220W
xtemal	W	202mm		302mm		510	0mm	610	Omm	71	Omm
dimensions (*4)	D	290mm		301mm		570	0mm	670mm		770mm	
excluding protrusions)	Н	440n	nm	455mm	555mm	590mm	690mm	590mm	690mm	590mm	690mm
Weight		11kg	13.3kg	14.5kg	15.5kg	37kg	40kg	55kg	58kg	66kg	69kg


SHOTmini™/SHOTMASTER™ SX&ΩX series Common specifications

■ Common specifications

Control method (*5)	PTP control and interpolation control					
Interpolation fund	otion	3-D line, 3-D circular arc/circle, 3-D elliptic arc/ellipse, spline					
Number of	General-purpose input	26 points					
input/output signal points	General-purpose output	26 points					
Program entry m	ethod	Teaching pendant, PC Japanese, English, Chinese 40000 steps (999 channels)					
Program display	language						
Program capacity	y (*6)						
	Internal	Internal memory					
Program storage system	External	Backup on PC with dispensing pattern editing software					
Program editing	software	MuCAD V (option)					

- *1 These values vary depending on the operations, weight and center of gravity of the loaded object, and other factors.
- *2 This value is measured by the method specified by Musashi (measurement method complies with JIS).
- *3 When options are not installed. The value varies with setting speed, setting acceleration/deceleration time, and operations.
- *4 W and D are the dimensions of the lower section of the case.
- *5 PTP control: Control to move each specified axis to the end coordinates at each speed. Interpolation control: Control to move each specified axis to the end coordinates at the total interpolated speed.
- *6 Main routine: 1 to 99 CH, sub routine: 100 to 999 CH
- * ΩX series has no (motor) step-out specifications.

■ Outside drawings



Angled approach

4-axis specification robot





Work rotation specification (custom)

Sc.

Easier maintenance

Nozzle adjuster

- Automated nozzle position offset adjustment after syringe replacement
- Significant reduction in downtime
 Nozzle position can be adjusted
- Nozzle position can be adjusted while dispensing program is running



SHOT mini M/ SHOTMASTER M 2X series

A fusion of dispensing technologies: "High Precision" and "High Rigidity"



SHOTmini™/SHOTMASTER™ ΩX series Line up







SHOTMASTER 300ΩX




SHOTMASTER 400ΩX



SHOTMASTER 500ΩX

■ Specifications

Item name		SHOTmi	ni 200ΩX	SHOTMAS	ΓER 300ΩX	SHOTMAS	TER 400ΩX	SHOTMASTER 500ΩX					
Model		SM200OMEGAX- 3A-SS SM200OMEGAX- 4A-SS		SM300OMEGAX- 3A-SS SM300OMEG 4A-SS		SM400OMEGAX- 3A-SS	SM4000MEGAX- 4A-SS	SM500OMEGAX- 3A-SS	M5000MEGAX 4A-SS				
No. of controlled axes		3-axis	4-axis	3-axis	4-axis	3-axis	4-axis	3-axis	4-axis				
	X-axis, Y-axis	200	mm	300	mm	400	mm	500	mm				
Travel ranges	Z-axis	80mm											
	W-axis	-	±360°	-	±360°	-	±360°	-	±360°				
	X-axis, Y-axis				1 to 50	00mm/s							
Setting range of PTP operation speed (*1)	Z-axis				00mm/s	nm/s							
operation speed (1)	W-axis		1 to 900°/s		1 to 900°/s		1 to 900°/s		1 to 900°/s				
Setting range	X-axis, Y-axis												
of interpolation	Z-axis	0.1 to 400mm/s											
operation speed (*1)	W-axis	- 0.1 to 900°		- 0.1 to 900		- 0.1 to 900°/s			0.1 to 900°/s				
	X-axis, Y-axis	±0.005mm											
Repetitive positioning accuracy (*2)	Z-axis	±0.005mm											
accuracy (2)	W-axis	-	±0.01°	-	±0.01°	-	±0.01°	=	±0.01°				
_oading capacity (*3)	Y-axis	20kg											
Loading Capacity (3)	Z-axis	15kg	12kg	15kg	12kg	15kg	12kg	15kg	12kg				
Rated voltage and free	quency				AC100-24	0V 50/60Hz							
Power consumption		130W 150W		130W	150W	180W	200W	180W	200W				
External	W	380mm		510mm		610mm		710mm					
dimensions (*4)	D	460	mm	570	mm	670	mm	770	mm				
(excluding protrusions)	Н	590mm	690mm	590mm	690mm	590mm	690mm	590mm	690mm				
Weight		30kg	33kg	40kg	43kg	55kg	58kg	66kg	69kg				



SHOTmini™/SHOTMASTER™ SX&ΩX Model Identification

:100×100mm :200×200mm 300:300×300mm :400×400mm

500:500×500mm

X, Y stroke

SM 200

SX

SX

OMEGAX

Series

3A

No. of Axes

Extension

SS function

SS

EXT100 SS 3A:3-axis None:Standard height None

3A-Z:3-axis, EXT50: +50mm strengthened Z-axis LEXT100: +100mm 4A:4-axis



MUSASHI's dispensing motion unit is capable of being mounted on automatic units.



CROSSMASTER™ SX series Line up













CROSSMASTER 230SX

CROSSMASTER 340SX

CROSSMASTER 460SX

CROSSMASTER 680SX

Controller

External operation BOX

■ Specifications

Item name		CROSSMASTER 230SX	CROSSMASTER 340SX	CROSSMASTER 460SX	CROSSMASTER 680SX							
Model		XM230SX-3A-L-SS XM230SX-3A-R-SS	XM340SX-3A-L-SS XM340SX-3A-R-SS	XM460SX-3A-L-SS XM460SX-3A-R-SS	XM680SX-3A-L-SS XM680SX-3A-R-SS							
No. of controlled axes		3-axis										
	X-axis	200mm	300mm	400mm	600mm							
Fravel ranges	Y-axis	300mm	400mm	600mm	800mm							
	Z-axis		150mm									
Setting range of	X-axis			1 to 470mm/s								
PTP operation	Y-axis	1 to 500	0mm/s	1 to 1000mm/s	1 to 830mm/s							
speed (*1)	Z-axis		1 to 30	00mm/s								
Setting range	X-axis		0.1 to 500mm/s		0.1 to 470mm/s							
of interpolation	Y-axis	0.1 to 500	0mm/s	0.1 to 999.9mm/s	0.1 to 830mm/s							
operation speed (*1)	Z-axis		0.1 to 3	00mm/s								
Repetitive	X-axis	±0.01mm										
oositioning	Y-axis		±0.01mm									
accuracy (*2)	Z-axis		1mm									
oading capacity (*3)		2.5kg										
Rated voltage and free	quency	Single phase, AC200-240 V 50/60 Hz										
Power consumption		200\	W	300W								
	W	565mm	635.5mm	760mm	1052.5mm							
External dimensions (excluding protrusions)	D	565mm	651mm	923mm	1123mm							
excluding protrusions)	Н	470m	nm	490mm								
Weight		25.5kg	28.5kg	44.5kg	67.5kg							

CROSSMASTER™ SX&ΩX series Common specifications

■ Common specifications


Control method	(*4)	PTP control and interpolation control 3-D line, 3-D circular arc/circle, 3-D elliptic arc/ellipse, spline 20 points				
Interpolation fund	ction					
Number of	General-purpose input					
input/output signal points	General-purpose output	23 points				
Program display	language	Teaching pendant, PC				
Program entry m	ethod	Japanese, English, Chinese 40000 steps (999 channels)				
Program capacit	y (*5)					
Drogram	Internal	Internal memory				
Program storage system	External	Backup on PC with dispensing pattern editing software				
Program editing	software	MuCAD V (option)				
Controller extern (excluding protrus		W450×D340×H265 mm				
Weight of dispens	e controller	18kg				

- *1 These values vary depending on the operations, weight and center of gravity of the loaded object, and other factors.
- *2 This value is measured by the method specified by Musashi (measurement method complies with JIS).
- *3 When options are not installed. The value varies with setting speed, setting acceleration/deceleration time, and operations.
- *4 PTP control: Control to move each specified axis to the end coordinates at each speed. Interpolation control: Control to move each specified axis to the end coordinates at the total interpolated speed.
- *5 Main routine: 1 to 99 CH, sub routine: 100 to 999 CH

*The XM460SX series, XM680SX series and XM Ω X series correspond to industrial robots.

*All models have no (motor) step-out specifications.

■ Outside drawings



Coordinated with dispenser

Synchro Speed™functionPAT.P **S**

Maintains a fixed line width, regardless of robot speed. Achieves high-quality dispensing automatically, without the need for any complex adjustments.



Right-angle dispensing Synchro Speed^T unction ON

Fully enhanced operability

Teaching pendant

- · Large, high-visibility screen with
- backlight 2-screen display makes programming easy
- · Equipped with interactive user-friendly interface function
 Stopwatch function
- Dispensing condition switching function
- ·Data transfer function between robots ·Available in Japanese, English, and Chinese





Powered with dispensing know-how for inline 3D dispensing.



CROSSMASTER™ ΩX series Line up













CROSSMASTER $330\Omega X$

CROSSMASTER 440ΩX

CROSSMASTER $560\Omega X$


CROSSMASTER $780\Omega X$

Controller

External operation BOX

■ Specifications

Item name		CROSSMAS	TER 3300X	CROSSMAS	STER 440OX	CROSSMAS	TER 560OX	CROSSMAS	TER 780OX			
Model		XM330OMEGAX-3A-L-SS	XM330OMEGAX-4A-L-SS	XM440OMEGAX-3A-L-SS	XM440OMEGAX-4A-L-SS	XM560OMEGAX-3A-L-SS	XM560OMEGAX-4A-L-SS	XM7800MEGAX-3A-L-SS XM7800MEGAX-3A-R-SS	XM7800MEGAX-4A-L-S			
No. of controlled axes		3-axis	4-axis	3-axis	4-axis	3-axis	4-axis	3-axis	4-axis			
	X-axis, Y-axis	300mm>	300mm	400mm>	<400mm	500mm	600mm	700mm>	«800mm			
Travel ranges	Z-axis	150mm										
<i>"</i> "	W-axis	-	±360°	_	±360°	_	±360°	-	±360°			
Setting range of	X-axis, Y-axis				1 to 50	0mm/s						
A STATE OF THE STA	Z-axis		1 to 400mm/s									
speed (*1)	W-axis	Ī	1 to 900°/s	-	1 to 900°/s –		1 to 900°/s	ī	1 to 900°/s			
Setting range	X-axis, Y-axis	0.1 to 500mm/s										
	Z-axis		0.1 to 400mm/s									
operation speed (*1)	W-axis	1	0.1 to 900°/s		0.1 to 900°/s	-	0.1 to 900°/s	_	0.1 to 900°/s			
Repetitive	X-axis, Y-axis	±0.005mm										
positioning	Z-axis											
accuracy (*2)	W-axis	_	±0.01°	-	±0.01°	-	±0.01°	-	±0.01°			
Loading capacity (*3)		10kg	7kg	10kg	7kg	10kg	7kg	10kg	7kg			
Rated voltage and frequency		Single phase, AC200-240 V 50/60 Hz										
Power consumption		300W	320W	300W	320W	300W	320W	300W	320W			
External	W	831	mm	931	mm	103	mm	1239mm				
dimensions (*4)	D	671	mm	771	mm	971mm		1171mm				
(excluding protrusions)	Н				630	mm						
Weight		80kg	83kg	91kg	94kg	120kg	123kg	143kg	146kg			



CROSSMASTER™ **SX&ΩX**

Model Identification

Type X, Y stroke					Se	Series No. of Axes		X-axis origin position		SS function		
X	XM 330				0	MEGAX - 3	BA	-	Ļ	-	S	S
			_ 230 :200×300mm 340 :300×400mm	460 :400×600mm 680 :600×800mm	_	SX		3-axis 4-axis		left :right		- None - SS
		330 :300×300mm 560 :500×600mm 440 :400×400mm 780 :700×800mm				OMEGAX *ΩX series are eq	quipped	with SS functio		*SS: Synchro S _I ndard *4A is a		

IMAGE MASTER™ 350PC<u>Smart</u>


Introducing essential units and new functions for micro-dispensing and reliable production.



Full 3D alignment and tracing function


The 3D alignment and tracing functions enable "tracing (Z correction)" that provides $XY\theta$ correction to suit tilted or deformed pallets or workpieces, and maintains a constant clearance with warping or

distortion. This ensures more reliable dispensing. Now the dispensing track can be corrected to suit fluctuations in the shape of the workpiece.






Different starting point, tilted work piece



Tilted work piece, pallet





Different sizes or shapes of work pieces

Camera teaching function

Align camera with dispensing position

Register coordinates

Program completed
Saving program creation time

Map screen

Target

Switch

1000

Camera screen

Reduced cycle time and greater yield

Easy liquid material changes and automatic correction

Syringe set-up function

Nozzle tip misalignment after changing liquid material can result in impact with work pieces or faulty dispensing.



Correct misalignment

Unique operation function to easily correct misaligned nozzles

Nozzle offset function
 Z-axis zero-point function

Tools required for reliable dispensing

Accessories unit

- Nozzle cleaning
- Test shot stage
- ·Nozzle touch sensor




Designed to handle various work shapes

Image processing and positioning recognition

- Pattern matching
- Center of gravity detection
- Edge detection NEW

Suitable for devices with irregular corner cuts



Production management

- Production log function Flexible start function
- Process monitoring Recipe function import/export function

Inspection

- Dimensions measurement function
 Dispensing track tracing function
- Image map creation functionQuick dispensed area
- •Quick dispensed area verification function

Outside drawings Measurement unit (mm) Desktop robot control box Image recognition unit Cartesian robot control box 363 52 280


Mucadv

Complex dispensing operations can now be programmed quickly and intuitively.



Powered with the leading dispensing know-how!

■ Saving editing time. ■ Intuitive drawing of dispensing patterns. ■ Edit dispensing patterns easily, even by beginners.



Entry by drawing Use the mouse to create the "drawing" program to be dispensed










and more

Useful functions

Generates multiple zigzag array program

Works straight away with various work layouts.

Includes "copy/rotate/flip" function for dispensing programs.



Linked

Entry by command


Create accurate programs by entering values

Useful functions

Pattern generator function

Configure any device layout on

Helps to reduce programming time significantly.



Automatic program creation

Automatically create dispensing programs from Gerber data.

Can also be created automatically from sources other Gerber data


•DXF data •Coordinate data



Cut out dispensing prohibited areas

Includes cut intermediate dispense area function to separate dispensing into dispense areas and prohibited areas.

*For conformal coating



Drawing by hand function

Programs can be created intuitively by hand (free line drawings).



System requirements

	os	Windows® 10, Windows® 8.1, Windows® 7							
	CPU	Pentium® 4 2 GHz equivalent or faster							
	Memory	512 MB or more (1 GB or more recommended)							
Display XGA (1024×768)		XGA (1024×768) or higher resolution							
Ī	Hard disk	100 MB or more available space							
	USB port	USB port x1 (SHOTMASTER ΩX/SX series, CROSSMASTER ΩX/SX series)							
	Serial port	Serial port x1 (SHOTMASTER DS/DSS series, other older models) Separate serial port x1/unit required when connecting the dispenser. USB serial converter can be used.							
	Applicable robots	SHOTMASTER $\Omega X/SX$ series, SHOTMASTER DS/DSS series, CROSSMASTER $\Omega X/SX$ series, also compatible with other older models							

^{*} This software is protected by the Copyright Act, and may not be copied or modified without prior consent of Musashi Engineering, Inc.

* Microsoft Windows is a registered trademark of Microsoft Corporation.

■ Connection image





Fully automatic dispensing machine



Váš dodavatel Musashi pro Česko a Slovensko

these material without prior written permission is strictly prohibited.



AMTECH, spol. s r.o.

Tel.: +420 541 225 215 E-mail: davkovani@amtech.cz Web: www.amtech-dispensing.cz

